



short-stroke cylinder

AEVC-80-25-A-P

Part number: 188307
Product to be discontinued

FESTO

No facility for sensing, piston-rod end with male thread.
Type to be discontinued. Available until 2026. See Support Portal for alternative products.



Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	80 mm
Spring return force, retracted	85 N
Based on the standard	ISO 6431 Hole pattern VDMA 24562
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	single-acting pushing action
Design structure	Piston Piston rod
Position detection	No
Operating pressure MPa	0.1 ... 1 MPa
Operating pressure	1 ... 10 bar 14.5 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	2,901 N
Moving mass	365 g
Product weight	1,354 g
Mounting type	with through hole with accessories Optional
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy Anodised
Material seals	NBR TPE-U(PU)
Material housing	Wrought Aluminium alloy Anodised
Material piston rod	High alloy steel