

Round cylinder DSEU-50-200-P-A

Part number: 188610

FESTO

End cap, with air connection perpendicular to cylinder axis
Products to be discontinued. Available until 2011.



Data sheet

Feature	Value
Stroke	200 mm
Piston diameter	50 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Cylinder barrel
Position detection	For proximity sensor
Variants	Single-ended piston rod
Operating pressure	1.5 ... 10 bar
Mode of operation	double-acting
Operating medium	Dried compressed air, lubricated or unlubricated
Corrosion resistance classification CRC	1
Ambient temperature	0 ... 80 °C
Theoretical force at 6 bar, return stroke	990 N
Theoretical force at 6 bar, advance stroke	1,178 N
Moving mass with 0 mm stroke	240.2 g
Additional weight per 10 mm stroke	40 g
Basic weight for 0 mm stroke	620 g
Mounting type	with accessories
Pneumatic connection	G1/4
Materials note	Contains PWIS substances
Materials information for cover	Wrought Aluminium alloy
Materials information for seals	TPE-U(PU)
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel