

mini guided drive DFC-10-25-P-A-GF

Part number: 189471

FESTO

For position sensing with plain-bearing guide.
Sensor bracket is included in scope of delivery



Data sheet

Feature	Value
Centre of gravity distance from working load to yoke plate	15 mm
Stroke	25 mm
Piston diameter	10 mm
Operating mode of drive unit	Yoke
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Guide	Plain-bearing guide
Design structure	Guide
Position detection	For proximity sensor
Operating pressure MPa	0.1 ... 1 MPa
Operating pressure	1 ... 10 bar
Max. speed	1 m/s
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-5 ... 60 °C
Impact energy in end positions	0.05 Nm
Max. torque Mx	0.4 Nm
Max. useful load as a function of the stroke at defined distance xs	12.2 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	35 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	47 N
Moving mass	27.2 g
Moving mass with 0 mm stroke	27.2 g
Additional mass factor per 10 mm of stroke	7.2 g
Product weight	125 g
Pneumatic connection	M5
Material cover	Wrought Aluminium alloy
Material seals	NBR
Material housing	Wrought Aluminium alloy
Material piston rod	High alloy steel, non-corrosive