

CPE10SC-M1BH-5L-M5-P

Solenoid valve

Data sheet

Part no.: 192506

Page:1

Feature	Data/description
Switching function	5/2-way valve
Switching function short code	5/2
Direction of flow reversible	No
Operating principle	Slide
Shape of function component	Piston
With exhaust flow control	Yes
Type of regulation	Indirect
Control type	Monostable
Type of reset	Air spring
Type of mounting	Screw
Installation position	Any
Nominal size	3 mm
Operating pressure min.	3 bar
Operating pressure max.	8 bar
Minimum ambient temperature	-5 °C
Maximum ambient temperature	50 °C
Minimum medium temperature	-5 °C
Maximum medium temperature	50 °C
Type of connection, air supply	Sub-base
Air connection type power port	Female thread
Connecting thread, working port	M 5
Type of connection, exhaust	Sub-base
Air connection type aux. pilot air suppl	Internal
Air connection type aux. pilot air exhau	Female thread
Connecting thread for aux. pilot air exh	M 3
Type pilot control air Supply and exhaus	External pilot air and air spring, ducted pilot ex
Actuation/reset	Single solenoid, air spring return
Manual override	Non-detenting (detenting with attachment)
Operating status display	No
Material of cap	PA-reinforced
Material of housing	AL, die-cast metal

CPE10SC-M1BH-5L-M5-P

Solenoid valve

Data sheet

Part no.: 192506

Page:2

Feature	Data/description
Material of seals	NBR-Elastomer
CT criterion	Free of copper and PTFE
Product weight	0,05 kg
Standard nominal flow rate 1 - 2	210 l/min
Standard nominal flow rate 2 - 3	210 l/min
Standard nominal flow rate 1 - 4	210 l/min
Standard nominal flow rate 4 - 3/5	210 l/min
Response time OFF/OVER (dom.)	11 ms
Response time OFF/OVER	15 ms
Voltage type	DC
Nominal voltage	24 V
Medium	Filtered compr. air (40 µm) (may be lubricated)
Degree of protection	IP65