

CPE10SC-M1BH-3GL-M7-QS-4

Solenoid valve

Data sheet

Part no.: 192529

Page:1

Feature	Data/description
Switching function	3/2-way valve, normally closed
Switching function short code	3/2
Direction of flow reversible	No
Operating principle	Slide
Shape of function component	Piston
With exhaust flow control	Yes
Type of regulation	Indirect
Control type	Monostable
Type of reset	Air spring
Type of mounting	Screw
Installation position	Any
Nominal size	3 mm
Operating pressure min.	3 bar
Operating pressure max.	8 bar
Minimum ambient temperature	-5 °C
Maximum ambient temperature	50 °C
Minimum medium temperature	-5 °C
Maximum medium temperature	50 °C
Type of connection, air supply	Female thread
Connecting thread, supply port	M 7
Air connection type power port	Push-in
Nominal size of tubing connection, working	4
Type of connection, exhaust	Female thread
Connecting thread, exhaust port	M 7
Air connection type aux. pilot air supply	Internal
Air connection type aux. pilot air exhaust	Female thread
Connecting thread for aux. pilot air exhaust	M 3
Type pilot control air Supply and exhaust	External pilot air and air spring, ducted pilot exhaust
Actuation/reset	Single solenoid, air spring return
Manual override	Non-detenting (detenting with attachment)
Operating status display	No

CPE10SC-M1BH-3GL-M7-QS-4

Solenoid valve

Data sheet

Part no.: 192529

Page:2

Feature	Data/description
Material of cap	PA-reinforced
Material of housing	AL, die-cast metal
Material of seals	NBR-Elastomer
CT criterion	Free of copper and PTFE
Product weight	0,074 kg
Standard nominal flow rate 1 - 2	195 l/min
Standard nominal flow rate 2 - 3	195 l/min
Response time OFF/OVER (dom.)	11 ms
Response time OFF/OVER	15 ms
Voltage type	DC
Nominal voltage	24 V
Medium	Filtered compr. air (40 µm) (may be lubricated)
Degree of protection	IP65