

round cylinder DSNU-50-25-P-A

Part number: 196000

FESTO

For position sensing, with elastic cushioning rings in end positions.
Various mounting options, with or without additional mounting components.



Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	50 mm
Piston rod thread	M16x1,5
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Cylinder barrel
Position detection	For proximity sensor
Operating pressure MPa	0.1 ... 1 MPa
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	989.6 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	1,178.1 N
Moving mass	476 g
Product weight	1,187 g
Mounting type	with accessories
Pneumatic connection	G1/4
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High alloy steel
Material cylinder barrel	High alloy steel, non-corrosive