

# axial kit EAMM-A-D50-60H

Part number: 2733796

FESTO

Suitable for electric drives.



## Data sheet

| Feature                  | Value            |
|--------------------------|------------------|
| Assembly position        | Any              |
| PWIS conformity          | VDMA24364-B2-L   |
| Storage temperature      | -25 ... 60 °C    |
| Relative air humidity    | 0 - 95 %         |
| Protection class         | IP40             |
| Ambient temperature      | -10 ... 60 °C    |
| Transferable torque      | 17 Nm            |
| Product weight           | 570 g            |
| Interface code, actuator | D50B             |
| Interface code, motor in | 60H              |
| Materials note           | Conforms to RoHS |