


# round cylinder CRHD-40- -PPV-A-MC-S6

Part number: 195550

FESTO

Corrosion-resistant, smooth bearing cap, end cap with clevis attachment, heat-resistant design to 120 °C

The S6 variant (heat resistant) is not intended for direct contact with food products due to the utilised seals and grease.



Exemplary representation



## Data sheet

Feature	Value
Stroke	10 ... 500 mm
Piston diameter	40 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	Heat resistant seals, max. 120°C
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B2-L
Food-safe	See Supplementary material information
Ambient temperature	-20 ... 120 °C
Cushioning length	19.5 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	633 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	754 N
Moving mass with 0 mm stroke	198 g
Additional mass factor per 10 mm of stroke	16 g
Basic weight for 0 mm stroke	1,154 g
Additional weight per 10 mm stroke	42 g
Pneumatic connection	G1/8
Material cover	High alloy steel, non-corrosive
Material seals	FPM
Material housing	High alloy steel, non-corrosive
Material piston rod	High alloy steel, non-corrosive