


bus node CPX-FB6

Part number: 195748
Product to be discontinued

for modular electrical terminal CPX.

Type to be discontinued. Available until 2027. See Support Portal for alternative products.



Data sheet

Feature	Value
Protocol	Interbus
Dimensions W x L x H	(including interlinking block) 50 mm x 107 mm x 50 mm
Product weight	125 g
Ambient temperature	-5 ... 50 °C
Storage temperature	-20 ... 70 °C
Protection class	IP65 IP67
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Material housing	PA-reinforced PC
Product-specific LED display	M: Modify, parameterisation PL: load supply PS: Electronics supply, sensor supply SF: system error
Bus-specific LED display	BA: bus active RC: Remotebus Check RD: Remotebus Disable TR: Transmit/Receive UL: Operating voltage
Device-specific diagnostics	Channel and module-oriented diagnostics Undervoltage modules Diagnostics memory
Control elements	DIL switches
Fieldbus interface	2 x Sub-D plug for self-assembly 2x M12x1, 5-pin, B-coded Sub-D socket and plug, 9-pin
Maximum address volume for inputs	12 Byte
Maximum address volume for outputs	12 Byte
Parameters configuring	Diagnostics behaviour Fail-safe reaction Forcing of channels Signal setup System parameters
Baud rate	500, 2000 kbit/s
Additional functions	- Acyclic data access via PCP channel Channel-oriented diagnostics via fieldbus Start-up parameterisation in normal text via fieldbus System status can be represented using process data Additional diagnostics interface for operator units
Operating voltage range DC	18 ... 30 V
Nominal operating voltage DC	24 V
Intrinsic current consumption at operating voltage	Typ. 200 mA