

round cylinder ESNU-32-25-P-A

Part number: 196377

FESTO

Based on DIN ISO 6432, for proximity sensing. Various mounting options, with or without additional mounting components. With elastic cushioning rings in the end positions.



Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	32 mm
Piston rod thread	M10x1,25
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Cylinder barrel
Position detection	For proximity sensor
Operating pressure MPa	0.12 ... 1 MPa
Operating pressure	1.2 ... 10 bar
Mode of operation	single-acting pushing action
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Spring return force, retracted	30 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	30 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	442.2 N
Moving mass	144 g
Moving mass with 0 mm stroke	121 g
Additional mass factor per 10 mm of stroke	9 g
Product weight	402 g
Basic weight for 0 mm stroke	370.5 g
Additional weight per 10 mm stroke	15.5 g
Mounting type	with accessories
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High alloy steel
Material cylinder barrel	High alloy steel, non-corrosive