



Pinch valve

VZQA-C-M22U-15-GG-V4V4E-4

Part number: 3022829

FESTO

Pneumatically actuated pinch valve in stainless steel, safety position open, G thread, DN15.



Data sheet

Feature	Value
Design structure	Pneumatically actuated pinch valve
Type of actuation	pneumatic
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	G1/2
Nominal diameter DN	15
Valve function	2/2 open, monostable
Flow direction	reversible
Pressure of medium	0 ... 0.4 MPa
Medium pressure	0 ... 4 bar
Pressure of medium psi	0 ... 58 psi
Operating pressure MPa	0.1 ... 0.65 MPa
Operating pressure	1 ... 6.5 bar 14.5 ... 94.25 psi
Nominal pressure of process valve	10
Differential pressure (MPa)	0.25 MPa
Differential pressure	2.5 bar
Differential pressure (psi)	36.25 psi
Burst pressure	1.6 MPa
Bursting pressure	16 bar
Burst pressure	232 psi
Overload pressure	0.78 MPa 7.8 bar
Overload pressure (psi)	113.1 psi
Type of reset	Rebound resilience
Type of piloting	With external control
Auxiliary pilot air port 12	G1/8
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:1]
Medium	Compressed air to ISO 8573-1:2010 [:::1] Water
Max. viscosity	4,000 mm ² /s
Medium temperature	-5 ... 100 °C
Ambient temperature	-5 ... 60 °C
Storage temperature	5 ... 20 °C
Flow rate Kv	5 m ³ /h
Switching time on	250 ms
Switching time off	250 ms
Materials note	Conforms to RoHS
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
Material housing	High alloy steel, non-corrosive
Material number for housing	1.4404

Feature	Value
Material housing cover	High alloy steel, non-corrosive
Material seals	FPM
Material shut-off element	EPDM
Product weight	431 g
Food-safe	See Supplementary material information
Material bowl	PA6