


# limit switch box

## SRBG-C1-N-1-P-M12

Part number: 3568055

FESTO

For electrical feedback and position monitoring of process valves actuated with pneumatic quarter turn actuators, inductive measuring principle.



### Data sheet

Feature	Value
Design	Angular
Based on the standard	EN 60947-5-2 VDI/VDE 3845
Authorisation	RCM Mark c UL us (OL)
CE mark (see declaration of conformity)	to EU directive for EMC in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC mark	KC-EMV
Materials note	Conforms to RoHS
Measuring principle	Inductive
Ambient temperature	-25 ... 70 °C
Switch output	PNP
Switching element function	Normally open contact
Max. switching frequency	500 Hz
Max. output current DC	100 mA
Voltage drop	≤ 3 V
Residual current	0 ... 0.5 mA
Short circuit strength	Pulsing
Operating voltage range DC	10 ... 30 V
Idle current	≤ 25 mA
Polarity protected	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, cable outlet	Straight
Electrical connection 1, design	Round
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Mounting type	Threaded
Assembly position	Any
Product weight	70 g
Material housing	PBT
Material screws	High alloy steel, non-corrosive
Ready status display	Green LED
Operating status display	Yellow LED
Storage temperature	-25 ... 70 °C
Protection class	IP67
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6
PWIS conformity	VDMA24364 zone III
Degree of contamination	3