


parallel kit EAMM-U-45-V25-40P-63

Part number: 4782056

★ Core product range

FESTO



Data sheet

Feature	Value
Size	45
Centre-to-centre distance	63 mm
Assembly position	Any
Gear unit ratio	1:1
Max. speed	3,600 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Mass moment of inertia	4.35 kgmm ²
No-load driving torque	0.05 Nm
Transferable torque	0.5 Nm
Product weight	253 g
Interface code, actuator	V25
Interface code, motor in	40P
Materials note	Conforms to RoHS