



motor cable

NEBM-H6G4-K-10-Q13N-LE4

Part number: 5219196

FESTO



Data sheet

Feature	Value
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Plug socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	Connection pattern H6, coded for the motor
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Operating voltage range DC	0 ... 300 V
Operating voltage range AC	0 ... 300 V
Acceptable current load at 40°C	9.5 A
Surge strength	2 kV
Cable length	10 m
Cable attribute	Standard
Test conditions of cable	Test conditions on request
Bending radius, fixed cable installation	≥ 74 mm
Bending radius, flexible cable installation	≥ 111 mm
Cable diameter	7.4 mm
Cable structure	4x0,79
Nominal conductor cross-section	0.79 mm ²
Nominal conductor cross section (AWG)	AWG18
Wire ends	Wire end ferrule
Protection class	IP20
Note on degree of protection	in assembled condition
Ambient temperature	-25 ... 90 °C
Ambient temperature with flexible cable installation	-25 ... 90 °C
CE mark (see declaration of conformity)	to EU directive low-voltage devices in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Materials note	Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	0 - No corrosion stress
Material cable sheath	TPE-E
Cable sheath colour	Black
Material housing	PA
Housing colour	white
Material insulation	TPE-E