


solenoid valve

MHE4-MS1H-3/20-QS-8-K

Part number: 525213

FESTO

individual valve, fast switching, with cable.



Data sheet

| Feature | Value |
|---|---|
| Valve function | 3/2 open, monostable |
| Type of actuation | electrical |
| Width | 18 mm |
| Standard nominal flow rate | 400 l/min |
| Operating pressure MPa | -0.09 ... 0.8 MPa |
| Operating pressure | -0.9 ... 8 bar |
| Design structure | Pressure-relieved poppet valve |
| Type of reset | mechanical spring |
| Protection class | IP65 |
| Authorisation | RCM Mark c UL us - Recognized (OL) |
| CE mark (see declaration of conformity) | to EU directive for EMC in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Nominal size | 4 mm |
| Grid dimension | 24 mm |
| Note on grid dimension | Minimum distance between the valves is 6 mm |
| Exhaust-air function | throttleable |
| Sealing principle | soft |
| Assembly position | Any |
| Manual override | Pushing |
| Type of piloting | direct |
| Flow direction | reversible with restrictions |
| Overlap | Underlap |
| Polarity protected | Bipolar |
| Additional functions | Spark arresting Reduction of holding current Protective circuit |
| Operating pressure, reversible | -0.09 ... 0.1 MPa -0.9 ... 1 bar -13.05 ... 14.5 psi |
| Maximum switching frequency | 210 Hz |
| Switching time off | 3.5 ms |
| Switching time on | 3.5 ms |
| Tolerance for Switching time OFF | +10 %/-40 % |
| Tolerance for Switching time ON | +10%/-30% |
| Measuring of the switching time at 1 Hz and above | 0.3 ms |
| Duty cycle | 100 % |
| Characteristic coil data | 24 V DC: low-current phase 2.125 W, high-current phase 8.5 W |
| Permissible voltage fluctuation | +/- 10 % |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |

| Feature | Value |
|---|--|
| Vibration resistance | Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Medium temperature | -5 ... 60 °C |
| Ambient temperature | -5 ... 60 °C |
| Product weight | 270 g |
| Electrical connection | Cable |
| Cable length | 2.5 m |
| Mounting type | with through hole |
| Pneumatic connection, 11 | QS-8 |
| Pneumatic connection, port 2 | QS-8 |
| Pneumatic connection, 33 | QS-8 |
| Materials note | Conforms to RoHS |
| Material seals | HNBR NBR |
| Material housing | Die-cast zinc, coated |
| Material cable sheath | PUR |
| Material screws | Galvanised steel |