

filter regulator MS6N-LFR

Part number: 527667

FESTO

With NPT thread



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	6
Series	MS
Actuator lock	Rotary knob with lock Rotary knob with integrated lock with accessories, lockable
Assembly position	Vertical +/- 5°
Grade of filtration	5 ... 40 µm
Condensate drain	fully automatic manual rotary semi-automatic
Design structure	Filter regulator with pressure gauge Filter regulator without pressure gauge
Controller function	Output pressure constant with secondary exhaust with return flow
Bowl guard	Plastic guard integrated as metal shell
Pressure gauge	Prepared for G1/4 Prepared for G1/8 with pressure sensor with pressure gauge
Operating pressure MPa	0.08 ... 2 MPa
Operating pressure	0.8 ... 20 bar
Pressure regulation range	0.3 ... 16 bar
Max. pressure hysteresis (MPa)	0.025 MPa
Max. pressure hysteresis	0.25 bar 3.625 psi
Standard nominal flow rate	2,000 ... 7,200 l/min
Authorisation	c UL us - Recognized (OL)
CE mark (see declaration of conformity)	to EU directive explosion protection (ATEX)
ATEX category Gas	II 2G
ATEX category Dust	II 2D
Explosion ignition protection type Gas	Ex h IIC T6 Gb X
Explosion ignition protection type Dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	-10°C ≤ Ta ≤ +60°C
Operating medium	Compressed air to ISO 8573-1:2010 [-:4:-] Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Food-safe	See Supplementary material information
Medium temperature	-10 ... 60 °C

Feature	Value
Ambient temperature	-10 ... 60 °C
Mounting type	Front panel installation Line installation with accessories Optional
Materials note	Conforms to RoHS
Material seals	NBR
Material filter	PE
Material housing	Aluminium die cast
Material membrane	NBR
Material separating plate	POM