


Motor controller SEC-ST-48-6-P01

Part number: 530069

FESTO

For stepper motor



Data sheet

Feature	Value
Controller operating mode	Bipolar-Chopper-Driver
Operating mode	Tenth step, 2000 step/U
Adjustable current reduction	0 or 70 via DIP switch
Step adjustment	Via DIP switch
Nominal current adjustment	DIP switches
Max. step frequency	40 kHz
Nominal current	1.25 ... 6 A
CE Symbol	according to EU-EMV guideline
Storage temperature	-10 ... 50 °C
Protection class	IP20
Ambient temperature	0 ... 40 °C
Product weight	610 g
Logic input working range	12 ... 30 V
Electrical connection	Screwed terminal
Mounting type	with top-hat rail