

lubricator

LOE-QS6-D-MICRO

Part number: 526314


Classic - do not use for new projects

FESTO

Connection plate with push-in connector

Modern alternatives can be found by entering the first four characters of the type code in the search field.

Type to be discontinued. Available until 2023. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|---|---|
| Size | Micro |
| Series | D |
| Assembly position | Vertical +/- 5° |
| Design structure | proportional standard mist lubricator |
| Max. oil capacity | 6.5 cm ³ |
| Operating pressure | 1 ... 10 bar |
| Minimum flow rate for lubricator function | 3 l/min |
| Standard nominal flow rate | 330 l/min |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Storage temperature | -10 ... 60 °C |
| Air purity class at output | Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 59 g |
| Mounting type | Line installation with accessories Optional |
| Pneumatic connection, port 1 | QS-6 |
| Pneumatic connection, port 2 | QS-6 |
| Materials note | Conforms to RoHS |
| Material housing | Aluminium die cast |
| Material bowl | PC |