


filter MS4N-LF

Part number: 527696

FESTO

With NPT thread



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	4
Series	MS
Assembly position	Vertical +/- 5°
Grade of filtration	5 ... 40 µm
Condensate drain	fully automatic manual rotary semi-automatic
Design structure	Sintered filter with centrifugal separator
Bowl guard	Plastic guard integrated as metal shell
Operating pressure	0 ... 14 bar
Standard nominal flow rate	1,000 ... 1,700 l/min
Authorisation	c UL us - Recognized (OL)
CE mark (see declaration of conformity)	to EU directive explosion protection (ATEX)
ATEX category Gas	II 2G
ATEX category Dust	II 2D
Explosion ignition protection type Gas	Ex h IIC T6 Gb X
Explosion ignition protection type Dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	-10°C ≤ Ta ≤ +60°C
Operating medium	Compressed air to ISO 8573-1:2010 [-:9:-] Compressed air to ISO 8573-1:2010 [7:9:-] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Food-safe	See Supplementary material information
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Mounting type	Line installation with accessories Optional
Materials note	Conforms to RoHS
Material of connecting plate	Aluminium die cast
Material seals	NBR
Material filter	PE
Material housing	Aluminium die cast
Material separating plate	POM