


MS4-EM-1/8-S-Z

start valve

| Feature | Data/description |
|---|---|
| Exhaust-air function | not throttleable |
| Type of actuation | manual |
| Sealing principle | soft |
| Assembly position | Any |
| Design structure | Piston slide |
| Type of piloting | direct |
| Pilot air supply | Internal |
| Flow direction | non reversible |
| Valve function | 3/2 Bistable |
| Switching position indicator | Knob direction = Flow direction |
| Operating pressure | 0 - 14 bar |
| b value | 0,5 |
| C value | 4,5 l/sbar |
| Standard nominal flow rate | 1.000 l/min |
| Operating medium | Compressed air |
| Corrosion resistance classification CRC | 2 |
| Medium temperature | -10 - 60 °C |
| Ambient temperature | -10 - 60 °C |
| Product weight | 0,29 kg |
| Mounting type | Optional Line installation with accessories |
| Pneumatic connection, port 1 | G1/8 |



MS4-EM-1/8-S-Z

start valve

| Feature | Data/description |
|---------------------------------|----------------------|
| Pneumatic connection, port 2 | G1/8 |
| Pneumatic connection, port 3 | Non-ducted |
| Materials note | Copper and PTFE-free |
| Materials information for seals | NBR |
| Materials information, housing | Aluminium die cast |