


Stepper motor MTR-ST-42-48S-AB

Part number: 530058

FESTO

Without gear unit/with brake.

Discontinued, available through 2008



Data sheet

Feature	Value
Operating voltage DC for brake	24 V
Insulation protection class	B
Power consumption, brake	6 W
Nominal voltage DC	48 V
Nominal motor current	1.8 A
CE mark (see declaration of conformity)	to EU directive for EMC
Storage temperature	-25 ... 60 °C
Relative air humidity	45 - 80 %
Protection class	IP54
Ambient temperature	0 ... 50 °C
Overall mass moment of inertia at power take-off	0.07 kgcm ²
Brake holding torque	0.4 Nm
Motor holding torque	0.34 Nm
Mass moment of inertia of brake	0.002 kgcm ²
Mass moment of inertia of rotor	0.068 kgcm ²
Permissible axial shaft load	7 N
Permissible radial shaft load	18 N
Product weight	490 g
Electrical connector system	Plug