


# Stepper motor MTR-ST-57-48S-AA

Part number: 530061

FESTO

Discontinued, available through 2008



## Data sheet

Feature	Value
Insulation protection class	B
Nominal voltage DC	48 V
Nominal motor current	3.1 A
CE mark (see declaration of conformity)	to EU directive for EMC
Storage temperature	-25 ... 60 °C
Relative air humidity	45 - 80 %
Protection class	IP54
Ambient temperature	0 ... 50 °C
Overall mass moment of inertia at power take-off	0.48 kgcm <sup>2</sup>
Motor holding torque	1.27 Nm
Mass moment of inertia of rotor	0.48 kgcm <sup>2</sup>
Permissible axial shaft load	10 N
Permissible radial shaft load	71 N
Product weight	1,200 g
Electrical connector system	Plug