


# Service unit combination MSB4-1/4:H7N3M2-WP-Z

Part number: 531090

FESTO

Comprising filter, pressure regulator, lubricator, wall mounting plate.  
Maximum output pressure 12 bar, 40 µm filter, with pressure gauge,  
metal bowl guard, fully automatic condensate drain, flow direction from  
right to left.



## Data sheet

Feature	Value
Size	4
Series	MS
Assembly position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	fully automatic
Design structure	Pressure regulator with gauge Standard filter Standard oil-mist lubricator
Bowl guard	Metal bowl guard
Pressure gauge	with pressure gauge
Pressure control range	1 ... 12 bar
Inlet pressure 1	1.5 ... 12 bar
Standard nominal flow rate	800 l/min
Operating medium	Filtered, unlubricated compressed air, 40 µm filtration Filtered, lubricated compressed air, 40 µm filtration
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Air purity class at output	5:7:- per DIN ISO 8573-1
Medium temperature	-10 ... 60 °C
Mounting type	with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4