

compact cylinder ADN-100-30-A-P-A

Part number: 536378

FESTO

Per ISO 21287, with position sensing and external piston rod thread



Data sheet

| Feature | Value |
|--|--|
| Stroke | 30 mm |
| Piston diameter | 100 mm |
| Piston rod thread | M16x1,5 |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Conforms to standard | ISO 21287 |
| Piston-rod end | Male thread |
| Position detection | For proximity sensor |
| Variants | Single-ended piston rod |
| Operating pressure MPa | 0.06 ... 1 MPa |
| Operating pressure | 0.6 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 ... 80 °C |
| Impact energy in end positions | 2.5 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 4,524 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 4,712 N |
| Moving mass with 0 mm stroke | 570 g |
| Additional mass factor per 10 mm of stroke | 25 g |
| Basic weight for 0 mm stroke | 2,154 g |
| Additional weight per 10 mm stroke | 98 g |
| Mounting type | with through hole with internal (female) thread with accessories Optional |
| Pneumatic connection | G1/8 |
| Materials note | Conforms to RoHS |
| Material of flange screw | Steel |
| Material cover | Die-cast aluminium, coated |
| Material seals | TPE-U(PUR) |
| Material piston rod | High alloy steel |
| Material cylinder barrel | Smooth-anodised wrought aluminium alloy |