



micro filter MS4N-LFM-1/4-ARM-DA

Part number: 536830

FESTO

0.01 µm filter, plastic bowl with plastic bowl guard, manual condensate drain, with differential pressure indicator, direction of flow from left to right.



Data sheet

| Feature | Value |
|---|---|
| Series | MS |
| Size | 4 |
| Design structure | Fibre filter |
| Grade of filtration | 0.01 µm |
| Condensate drain | manual rotary |
| Operating pressure | 0 ... 14 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [6:8:4] Inert gases |
| Air purity class at output | Compressed air in accordance with ISO8573-1:2010 [1:7:2] |
| Max. standard flow rate for air quality class | 360 l/min |
| Min. standard flow rate for air quality class | 54 l/min |
| Filter efficiency | 99.9999 % |
| Max. condensate volume | 19 ml |
| Bowl guard | Plastic guard |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Food-safe | See Supplementary material information |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Storage temperature | -10 ... 60 °C |
| Residual oil content | 0.01 mg/m ³ |
| Differential pressure display | Visual indicator |
| Mounting type | Line installation with accessories Optional |
| Assembly position | Vertical +/- 5° |
| Pneumatic connection, port 1 | 1/4 NPT |
| Pneumatic connection, port 2 | 1/4 NPT |
| Material housing | Aluminium die cast |
| Material filter | Boron silicate fibre |
| Material bowl | PC |
| Material seals | NBR |
| Materials note | Conforms to RoHS |
| Product weight | 190 g |