

lubricator MS12-LOE-G-U

Part number: 537156

FESTO

Metal bowl, direction of flow: from left to right.



Data sheet

Feature	Value
Size	12
Series	MS
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	1,500 cm ³
Bowl guard	integrated as metal shell
Operating pressure	1 ... 16 bar
Minimum flow rate for lubricator function	400 l/min
Standard nominal flow rate	20,000 ... 22,000 l/min
Operating medium	Air quality class 5:7:- per DIN ISO 8573-1
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Medium temperature	0 ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	0 ... 60 °C
Product weight	6,500 g
Mounting type	Line installation With mounting bracket Optional
Pneumatic connection, port 1	Internal
Pneumatic connection, port 2	Internal
Material of cover	PA
Material seals	NBR
Material housing	Aluminium die cast
Material bowl	Wrought Aluminium alloy