



proximity sensor SIEN-M30B-NS-K-L-PA

Part number: 538328
Product to be discontinued

FESTO

With cable, flush mounting

Type to be discontinued. Available until 2024. See Support Portal for alternative products.



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Authorisation	RCM Mark c UL us - Listed (OL)
CE mark (see declaration of conformity)	to EU directive for EMC
Measuring principle	Inductive
Nominal switching distance	10 mm
Guaranteed switching distance	8.1 mm
Reduction factors	Aluminium = 0.35 to 0.5 Stainless steel, St 18/8 = 0.6 to 1.0 Copper = 0.25 to 0.45 Brass = 0.35 to 0.5 Steel, St 37 = 1.0
Ambient temperature	-25 ... 70 °C
Repetition accuracy	0.2 mm
Switch output	NPN
Switching element function	Normally open contact
Hysteresis	0.3 ... 1.5 mm
Max. switching frequency, DC	500 Hz
Max. output current	200 mA
Voltage drop	≤ 1.8 V
Short circuit strength	Pulsing
Operating voltage range DC	10 ... 30 V
Residual ripple	10 %
Idle current	≤ 15 mA
Polarity protected	for all electrical connections
Electrical connection	3-core Cable
Cable length	2.5 m
Material cable sheath	PVC
Material insulation	PVC
Size	M30
Mounting type	with lock nut
Tightening torque	5 Nm
Type of installation	flush
Product weight	158 g
Material housing	PA-reinforced
Operating status display	Yellow LED
Ambient temperature with flexible cable installation	0 ... 70 °C
Protection class	IP65 IP67
Corrosion resistance classification CRC	4 - Very high corrosion stress