


multi-pin plug CPV14-VI-P2-1/8-C

Part number: 539498
Classic - do not use for new projects

FESTO

For valve terminal CPV.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

| Feature | Value |
|---|--|
| CE mark (see declaration of conformity) | to EU directive explosion protection (ATEX) |
| UKCA marking (see declaration of conformity) | To UK EX instructions To UK RoHS instructions |
| Explosion protection certification outside the EU | EPL Db (GB) EPL Db (IEC-EX) EPL Dc (IEC-EX) EPL Gb (GB) EPL Gb (IEC-EX) EPL Gc (IEC-EX) |
| Certificate issuing department | IECEX TUR 12.0002X TÜV 06 ATEX 7334 X TÜV 21 UKEX 7013 X |
| ATEX category Gas | II 2G |
| ATEX category Dust | II 2D |
| Explosion ignition protection type Gas | Ex eb IIC Gb |
| Explosion ignition protection type Dust | Ex tb IIIC Db |
| Explosion-proof ambient temperature | -10°C ≤ Ta ≤ +60°C |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Product weight | 500 g |
| Materials note | Conforms to RoHS Halogen-free Free of copper |
| Material seals | NBR |
| Material plate | Wrought Aluminium alloy |