


# Handling module HSW-10-AE-IO-SD-GE

Part number: 540253

FESTO

Pick and Place for repositioning parts at a 90° angle, with motor unit, I/O connection, protective cover and right-angle gear unit.



## Data sheet

Feature	Value
Working stroke	9 ... 15 mm
Size	10
Max. linear stroke at 90° swivel angle	90/90 mm
Z stroke	80 ... 100 mm
Cushioning	noise absorption through buffer Predefined braking ramp
Assembly position	Any
Type of gear unit	Planetary gear unit
Design structure	linear guide plus rotating bearing Motor unit guided motion sequence
Gear unit ratio	13,73:1
Rotor position sensor	Optical encoder
Temperature monitoring	Shutdown at over-temperature (>80°)
Minimum cycle time	0.8 s
Repetition accuracy, intermediate positions	< 2 mm
Repetition accuracy, end positions	+/-0,02 mm
Number of increments per revolution	300
Display resolution	128x64 Pixel
Insulation protection class	F
Max. current, digital logic outputs	200 mA
Nominal motor power	17.5 W
Nominal motor current	0.73 A
Parameters configuring interface	RS232 (9600 Baud)
Nominal voltage DC	24 V
Peak current	2.1 A
Permissible voltage fluctuation	+/- 10 %
CE mark (see declaration of conformity)	to EU directive for EMC
Protection class	IP54
Ambient temperature	0 ... 50 °C
Max. torque Mx	0.6 Nm
Max. torque My	0.6 Nm
Max. torque Mz	0.6 Nm
Maximum process force in Y direction	30 N
Theoretical effective power in Z direction	15 N
Product weight	2,520 g
Mounting type	With through-hole and centring sleeve
Materials note	Contains PWIS substances
Material information, stops	High alloy steel
Materials information for cover	Wrought Aluminium alloy Anodised
Material information, spring pressure piece	High alloy steel
Materials information for sub-base	Wrought Aluminium alloy

Feature	Value
	Anodised
Material information, holder	Wrought Aluminium alloy Anodised
Materials information for cross-guide	Heat-treatment steel
Material information, swivel lever	Case-hardened steel Burnished
Material information, slotted guide plate	Case-hardened steel Hardened
Material information, sensor rail	Wrought Aluminium alloy Anodised
Material information, ridge	Wrought Aluminium alloy Anodised
Material information, adjusting screw	High alloy steel