


intermediate position module DADM-DGC-32-A

Part number: 541701

FESTO

For DGC and DGCI linear drives.



Data sheet

Feature	Value
Size	32
Assembly position	Any
Position detection	For proximity sensor
Operating pressure MPa	0.25 ... 0.8 MPa
Operating pressure	2.5 ... 8 bar 36.25 ... 116 psi
Max. impact speed	3 m/s
Max. swivel time	100 ms
Repetition accuracy	0.02 mm
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Product weight	530 g
Mounting type	Clamped to cylinder DGC
Pneumatic connection	QS-4
Materials note	Conforms to RoHS
Material stop screw	Steel Galvanised
Material seals	NBR
Material housing	Wrought Aluminium alloy Anodised
Material lever	High alloy steel, non-corrosive
Material clip	High alloy steel, non-corrosive
Material nut	Steel Galvanised
Precision adjustment	2 mm
Mode of operation	double-acting