


Pick&Place DHSP-HMP25-HMP20

Part number: 542978

FESTO

comprising modular handling axes, for precise and stiff applications with long travel. Defined interfaces to Festo's rotary and gripper range. Order as a mounting kit or completely assembled and installed.

Please click above on symbol FAX request, to obtain a non-binding offer to fulfil your requirements.



Data sheet

Feature	Value
Assembly	Pick&Place 3.0
Effective load	0 ... 6 kg
Drive unit, Z axis	HMP-20
Drive system, Z axis	Pneumatic
Intermediate position, Z axis	x1
Stroke, Z axis	0 ... 400 mm
Repetition accuracy in the end position, Z axis	± 0,01 mm
Repetition accuracy in the intermediate position, Z axis	± 0,01 mm
Drive unit, Y axis	HMP-25
Drive system, Y axis	Pneumatic
Intermediate position, Y axis	x1
Stroke, Y axis	0 ... 400 mm
Repetition accuracy in the end position, Y axis	± 0,02 mm
Repetition accuracy in the intermediate position, Y axis	± 0,02 mm