


# Electro-cylinder DNCE-40-100-BS-"5"P-Q

Part number: 543127

FESTO

with ball-bearing spindle drive and non-rotating piston rod.



## Data sheet

Feature	Value
Working stroke	100 mm
Size	40
Stroke	100 mm
Stroke reserve	0 mm
Piston rod thread	M12x1,25
Reversing backlash	0.05 mm
Spindle diameter	12 mm
Spindle pitch	5 mm/U
Max. angular deflection of piston rod +/-	0.25 deg
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Assembly position	Any
Motor type	Stepper motor Servomotor
Position detection	For proximity sensor
Design structure	Electro-cylinder with ball screw
Spindle type	Ball screw spindle
Variants	Non-rotating piston rod
Protection against torque/guide	with plain-bearing guide
Max. acceleration	6 m/s <sup>2</sup>
Max. speed	0.25 m/s
Repetition accuracy	+/-0,02 mm
Duty cycle	100%
Corrosion resistance classification CRC	0
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Impact energy in end positions	0.0002 J
Permanent drive torque	0.8 Nm
Permanent feed force	420 N
Max. drive torque	0.9 Nm
Max. torque for protection against rotation	1 Nm
Max. torque M <sub>x</sub>	1 Nm
Max. radial force at drive shaft	260 N
Max. static axial force F <sub>x</sub>	1,400 N
Max. feed force F <sub>x</sub>	525 N
No-load driving torque	0.12 Nm
Reference value for working load, horizontal	50 kg
Reference value for working load, vertical	25 kg
Mass moment of inertia J <sub>H</sub> per metre of stroke	0.1163 kgcm <sup>2</sup>
Mass moment of inertia J <sub>L</sub> per kg of working load	0.0063 kgcm <sup>2</sup>
Mass moment of inertia, J <sub>O</sub>	0.1304 kgcm <sup>2</sup>
Moving mass with 0 mm stroke	310 g

Feature	Value
Additional weight per 10 mm stroke	45.5 g
Basic weight for 0 mm stroke	1,270 g
Additional mass factor per 10 mm of stroke	8.9 g
Mounting type	with internal (female) thread with accessories
Materials note	Contains PWIS substances Conforms to RoHS
Materials information for cover	Aluminium casting Painted
Materials information for seals	NBR
Materials information, housing	Wrought Aluminium alloy Smooth anodised
Materials information for piston rod	High alloy steel, non-corrosive
Material information, spindle nut	Roller bearing steel
Material information, spindle	Roller bearing steel
Materials information for cylinder barrel	Wrought Aluminium alloy Smooth anodised