



flow sensor SFET-F500-L-W18-B-K1

Part number: 538533

FESTO

Flow rate transducer



Data sheet

Feature	Value
Authorisation	C-Tick
CE mark (see declaration of conformity)	to EU directive for EMC
Materials note	Contains PWIS substances
Flow measurement range initial value	5 l/min
Flow measurement range final value	50 l/min
Operating pressure	-0.7 ... 7 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [1:4:2] Nitrogen
Medium temperature	0 ... 50 °C
Ambient temperature	0 ... 50 °C
Switch-on time	50 ms
Analogue output	1 - 5 V
Linearity error, FS	5 %
Analogue value reproducibility, FS	3 %
Load resistance	50 kOhm
Operating voltage range DC	12 ... 24 V
Electrical connection	Cable
Cable length	1 m
Materials information, cable sheaths	PVC
Mounting type	with through hole
Assembly position	Vertical Horizontal
Pneumatic connection	Female thread G1/8
Product weight	90 g
Materials information, housing	Aluminium PA
Ready status display	LED
Protection class	IP40
Corrosion resistance classification CRC	2 - Moderate corrosion stress