


**mini slide**  
**DGSL-10- -**  
 Part number: 543905



**Data sheet**

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	10 ... 100 mm
Piston diameter	12 mm
Operating mode of drive unit	Yoke
Cushioning	Short elastic cushioning rings/pads at both ends No cushioning P: Flexible cushioning rings/plates at both ends P1: Flexible cushioning rings/plates with stop at both ends Self-adjusting progressive shock absorber at both ends, with reducing sleeve Y3: Shock absorber at both ends, progressive
Assembly position	Any
Guide	Ball bearing cage guide
Design structure	Yoke Piston Piston rod Slide
Position detection	For proximity sensor
Operating pressure MPa	0.15 ... 0.8 MPa
Operating pressure	1.5 ... 8 bar
Max. speed	0.8 m/s
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	51 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	68 N
alternative connections	See product drawing
Mounting type	with through hole
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	HNBR
Material housing	Wrought Aluminium alloy
Material piston rod	High alloy steel, non-corrosive