

round cylinder DSNU-1/2"-1"-P-A-B

Part number: 546386

FESTO

Based on DIN ISO 6432, for position sensing Various mounting options, with or without additional mounting components. With flexible cushioning rings in the end positions.



Data sheet

| Feature | Value |
|--|---|
| Stroke | 1 " |
| Piston diameter | 1/2" |
| Piston rod thread | 10-32 UNF-2A |
| Based on the standard | ISO 6432 |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Piston-rod end | Male thread |
| Design structure | Piston Piston rod |
| Position detection | For proximity sensor |
| Variants | Single-ended piston rod |
| Operating pressure MPa | 0.1 ... 1 MPa |
| Operating pressure | 1 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -4 ... 176 °F |
| Impact energy in end positions | 0.0516 ft-lbf |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 11.4 lbf |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 15.3 lbf |
| Moving mass with 0 mm stroke | 0.653 oz |
| Additional mass factor per 10 mm of stroke | 0.071 oz |
| Basic weight for 0 mm stroke | 2.646 oz |
| Additional weight per 10 mm stroke | 0.141 oz |
| Mounting type | with accessories |
| Pneumatic connection | 10-32 UNF-2B |
| Material cover | Wrought Aluminium alloy |
| Material seals | NBR TPE-U(PU) |
| Material piston rod | High alloy steel, non-corrosive |
| Material cylinder barrel | High alloy steel, non-corrosive |