

basic valve



LFR-D-5M-MAXI

Part number: 546468
 Classic - do not use for new projects



With metal bowl guard without pressure gauge, degree of filtration 5 µm. With automatic condensate drain.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
Size	Maxi
Series	D
Actuator lock	Rotary knob with lock
Assembly position	Vertical +/- 5°
Grade of filtration	5 µm
Condensate drain	manual rotary
Design structure	Filter regulator without pressure gauge
Max. condensate volume	2.72 oz(l)
Bowl guard	Metal bowl guard
Pressure gauge	Prepared for G1/4
Operating pressure	13.8 ... 240 Psi
Pressure regulation range	6.9 ... 180 Psi
Max. pressure hysteresis	6 Psi
Standard nominal flow rate	262.5 cfm
Operating medium	Compressed air to ISO 8573-1:2010 [:-9:-] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	14 ... 140 °F
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [6:8:4] Inert gases
Medium temperature	14 ... 140 °F
Ambient temperature	14 ... 140 °F
Product weight	47.95 oz
Mounting type	Line installation with accessories Optional
Materials note	Conforms to RoHS
Material housing	Zinc die-casting
Material bowl	PC