


proximity sensor SME-10M-DS-24V-E-2,5-Q-OE

Part number: 551366

FESTO

Suitable for C-slot.



Data sheet

Feature	Value
Design	for round slot
Conforms to standard	EN 60947-5-2
Authorisation	RCM Mark
CE mark (see declaration of conformity)	to EU directive for EMC in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Special characteristics	Oil resistant
Materials note	Conforms to RoHS Halogen-free
Instructions for use	Support / Actuator-sensor overview "The right sensor for the actuator"
Measured variable	Position
Measuring principle	Reed magnetic
Ambient temperature	-40 ... 70 °C
Repetition accuracy	0.2 mm
Switch output	with contact, bipolar
Switching element function	Normally open contact
Switch-on time	≤ 1.2 ms
Switch-off time	≤ 1 ms
Max. switching frequency	50 Hz
Max. output current	300 mA
Max. output current in mounting kits	50 mA
Max. contact rating AC	9 VA
Max. contact rating DC	9 W
Max. switching capacity DC in mounting kits	1.5 W
Max. switching capacity AC in mounting kits	1.5 VA
Voltage drop	≤ 1.5 V
Short circuit strength	No
Overload withstand capability	Not available
Nominal operating voltage DC	24 V
Operating voltage range AC	5 ... 30 V
Operating voltage range DC	5 ... 30 V
Polarity protected	No
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	3
Connector exit direction	Lateral
Test conditions of cable	Bending strength according to Festo standard Test conditions on request Torsion resistance: > 300,000 cycles, ±270°/0.1 m Energy chain: > 5 million cycles, bending radius 28 mm
Cable length	2.5 m
Cable attribute	Suitable for energy chains/robot applications
Material cable sheath	TPE-U(PUR)

Feature	Value
Mounting type	Tightened Insertable in slot from above
Max. tightening torque	0.4 Nm
Assembly position	Any
Product weight	16.8 g
Material housing	PA-reinforced High alloy steel, non-corrosive
Operating status display	Yellow LED
Ambient temperature with flexible cable installation	-20 ... 70 °C
Protection class	IP65 IP68
PWIS conformity	VDMA24364-B2-L