

# adsorption dryer

## PDAD-13-G3/8

Part number: 552171

FESTO

For dry and clean compressed air.



## Data sheet

Feature	Value
Assembly position	Vertical Horizontal
Design structure	Cold-regeneratable adsorption dryer
Inlet pressure 1	4 ... 16 bar
KC mark	KC-EMV
CE mark (see declaration of conformity)	to EU directive for EMC to EU directive low-voltage devices
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK instructions for EMC
Operating medium	Compressed air to ISO 8573-1:2010 [6:-:4]
Note on operating and pilot medium	Lubricated operation not possible No water in liquid form
Pressure dew point	-40 °C
Pressure dew point for reduced rate of flow	-70 °C
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-20 ... 60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [2:1:2] at -70°C Compressed air to ISO 8573-1:2010 [2:2:2] at -40°C
Medium temperature	2 ... 50 °C
Ambient temperature	5 ... 50 °C
Product weight	14,000 g
Mounting type	with accessories
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Materials note	Conforms to RoHS
Material housing	Wrought Aluminium alloy