

# compact cylinder ADNGF-16-20-P-A

Part number: 554215

FESTO

According to ISO 21287, with plain-bearing guide, piston rod secured against rotation by means of guide rods and yoke plate.



## Data sheet

| Feature  | Value   |
|--|---|
| Stroke   | 20 mm   |
| Piston diameter  | 16 mm   |
| Based on the standard                                    | ISO 21287   |
| Cushioning   | P: Flexible cushioning rings/plates at both ends                            |
| Assembly position  | Any   |
| Design structure   | Piston<br>Piston rod<br>Profile barrel                                      |
| Position detection                                       | For proximity sensor  |
| Protection against torque/guide                          | Guide rod with yoke   |
| Operating pressure MPa                                   | 0.15 ... 1 MPa  |
| Operating pressure                                       | 1.5 ... 10 bar  |
| Mode of operation  | double-acting   |
| Operating medium   | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                       | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC                  | 2 - Moderate corrosion stress   |
| PWIS conformity  | VDMA24364-B1/B2-L   |
| Ambient temperature                                      | -20 ... 80 °C   |
| Impact energy in end positions                           | 0.15 J  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 90 N  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance    | 121 N   |
| Moving mass with 0 mm stroke                             | 29 g  |
| Additional mass factor per 10 mm of stroke               | 6 g   |
| Basic weight for 0 mm stroke                             | 93 g  |
| Additional weight per 10 mm stroke                       | 16 g  |
| Pneumatic connection                                     | M5  |
| Materials note   | Conforms to RoHS  |
| Material of flange screw                                 | Steel   |
| Material cover   | Anodised wrought aluminium alloy  |
| Material seals   | TPE-U(PUR)  |
| Material end plate                                       | Anodised wrought aluminium alloy  |
| Material piston rod                                      | High alloy steel  |
| Material cylinder barrel                                 | Smooth-anodised wrought aluminium alloy                                     |