

semi-rotary drive

DAPS-0030-090-R-F04-T6

Part number: 553173

FESTO

double-acting, air connection to VDI/VDE 3845 Namur valves, direct flange mounting, version with handwheel, low temperature version.



Data sheet

| Feature | Value |
|---|--|
| Size of actuator | 0030 |
| Flange hole pattern | F04 |
| Swivel angle | 90 deg |
| End-position adjustment range at 0° | -1 ... 9 deg |
| Shaft connection depth | 13.2 mm |
| Fitting connection conforms to standard | ISO 5211 |
| Cushioning | No cushioning |
| Assembly position | Any |
| Mode of operation | double-acting |
| Design structure | Yoke kinematics |
| Position detection | No |
| Closing direction | right-closing |
| Valve connection conforms to standard | VDI/VDE 3845 (NAMUR) |
| Safety Integrity Level (SIL) | Product can be used in SRP/CS up to SIL 2 low demand |
| Operating pressure MPa | 0.3 ... 0.84 MPa |
| Operating pressure | 3 ... 8.4 bar |
| Nominal operating pressure | 0.56 MPa 5.6 bar |
| Max. swivel frequency at 0.6 MPa (6 bar, 87 psi) | 1 Hz |
| CE mark (see declaration of conformity) | to EU directive explosion protection (ATEX) |
| UKCA marking (see declaration of conformity) | To UK EX instructions |
| Certificate issuing department | TÜV Nord 212170801 |
| ATEX category Gas | II 2G |
| ATEX category Dust | II 2D |
| Explosion ignition protection type Gas | Ex h IIC T6...T3 Gb X |
| Explosion ignition protection type Dust | Ex h IIIC T85°C...T200°C Db X |
| Explosion-proof ambient temperature | -50°C ≤ Ta ≤ +60°C |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 3 - High corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Ambient temperature | -50 ... 60 °C |
| Torque at rated operating pressure and 0° rotation angle | 30 Nm |
| Torque at nominal operating pressure with 50° swivel angle | 15 Nm |
| Torque at nominal operating pressure with 90° swivel angle | 22.5 Nm |
| Note about the torque | The operating torque of the actuator must not be higher than the maximum permissible torque listed in ISO 5211, with reference to the size of the mounting flange and of the coupling. |
| Air consumption at 0.6 MPa (6 bar, 87 psi) per cycle 0°-nominal swivel angle-0° | 1.05 l |
| Product weight | 1,000 g |
| Shaft connection | T11 |
| Pneumatic connection | G1/8 |

| Feature | Value |
|---------------------------|-------------------------|
| Materials note | Conforms to RoHS |
| Material cover | Wrought Aluminium alloy |
| Material seals | FVMQ PTFE reinforced |
| Material housing | Wrought Aluminium alloy |
| Material screws | High alloy steel |
| Material shaft | High alloy steel |
| Material number for shaft | 1.4305 |