


Encoder cable NEBM-T1G12-T1G12-5

Part number: 556797

FESTO

For connecting the motor and controller



Data sheet

| Feature | Value |
|--|--|
| Cable attribute | Suitable for chain link trunking |
| Degree of contamination | 3 |
| Protection class | in assembled condition IP65 |
| Ambient temperature with flexible cable installation | -40 ... 90 °C |
| Ambient temperature | -50 ... 90 °C |
| Min. cable bending radius | 82 mm |
| Cable structure | Shielded 5 x (2 x 0,34 mm ²) + 2 x 0,5mm ² |
| Cable diameter | 11 mm |
| Cable length | 5 m |
| Materials note | Contains PWIS substances Conforms to RoHS |
| Materials information, cable sheaths | TPE-U(PUR) |