


spindle axis EGC-70- -BS-KF

Part number: 556807

FESTO

With recirculating ball bearing guide



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

| Feature | Value |
|---|--|
| Working stroke | 50 ... 1,000 mm |
| Size | 70 |
| Spindle diameter | 12 mm |
| Spindle pitch | 10 mm/U |
| Assembly position | Any |
| Guide | Recirculating ball bearing guide |
| Design structure | Electromechanical linear axis with recirculating ball bearing spindle |
| Motor type | Stepper motor Servomotor |
| Spindle type | Ball screw spindle |
| Max. acceleration | 15 m/s ² |
| Max. speed | 0.5 m/s |
| Repetition accuracy | ±0,02 mm |
| Duty cycle | 100 % |
| PWIS conformity | VDMA24364-B2-L |
| Protection class | IP40 |
| Ambient temperature | -10 ... 60 °C |
| Area moment of inertia 2nd degree Ix | 419E+03 mm ⁴ |
| Area moment of inertia 2nd degree Iy | 578E+03 mm ⁴ |
| Area moment of inertia 2nd degree Iz | 419E+03 mm ⁴ |
| Max. force Fy | 1,850 N |
| Max. force Fz | 1,850 N |
| Max. torque Mx | 16 Nm |
| Max. radial force at drive shaft | 220 N |
| Max. feed force Fx | 400 N |
| Torsional mass moment of inertia It | 88E+03 mm ⁴ |
| Mass moment of inertia JH per metre of stroke | 0.142 kgcm ² |
| Feed constant | 10 mm/U |
| Material of end caps | Wrought Aluminium alloy Anodised |
| Material of moment compensator | Wrought Aluminium alloy Anodised |
| Material of profile | Wrought Aluminium alloy Anodised |
| Materials note | Conforms to RoHS |
| Material drive cover | Wrought Aluminium alloy Anodised |
| Material guide slide | Steel |
| Material guide rail | Steel |
| Material slide | Wrought Aluminium alloy Anodised |
| Material spindle nut | Steel |
| Material spindle | Steel |