


# spindle axis EGC-120- -BS-KF

Part number: 556809

FESTO

With recirculating ball bearing guide



Exemplary representation

## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Working stroke	50 ... 2,500 mm
Size	120
Spindle diameter	25 mm
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Electromechanical linear axis with recirculating ball bearing spindle
Motor type	Stepper motor Servomotor
Spindle type	Ball screw spindle
Max. acceleration	15 m/s <sup>2</sup>
Max. speed	0.6 ... 1.5 m/s
Repetition accuracy	±0,02 mm
Duty cycle	100 %
PWIS conformity	VDMA24364-B2-L
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Area moment of inertia 2nd degree Ix	5,010E+03 mm <sup>4</sup>
Area moment of inertia 2nd degree Iy	5,820E+03 mm <sup>4</sup>
Area moment of inertia 2nd degree Iz	5,010E+03 mm <sup>4</sup>
Max. force Fy	6,890 N
Max. force Fz	6,890 N
Max. torque Mx	144 Nm
Max. radial force at drive shaft	500 N
Max. feed force Fx	1,500 N
Torsional mass moment of inertia It	1,430E+03 mm <sup>4</sup>
Mass moment of inertia JH per metre of stroke	2.756 kgcm <sup>2</sup>
Feed constant	10 ... 25 mm/U
Pneumatic port on clamping unit	M5
Material of end caps	Wrought Aluminium alloy Anodised
Material of moment compensator	Wrought Aluminium alloy Anodised
Material of profile	Wrought Aluminium alloy Anodised
Materials note	Conforms to RoHS
Material drive cover	Wrought Aluminium alloy Anodised
Material guide slide	Steel
Material guide rail	Steel
Material slide	Wrought Aluminium alloy Anodised
Material spindle nut	Steel
Material spindle	Steel