

compact cylinder

ADNGF-1 1/4"-1 1/4"-P-A

Part number: 557236

FESTO

According to ISO 21287, with plain-bearing guide, piston rod secured against rotation by means of guide rods and yoke plate.



Data sheet

Feature	Value
Stroke	1.25 "
Piston diameter	1 1/4"
Based on the standard	ISO 21287
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Profile barrel
Position detection	For proximity sensor
Protection against torque/guide	Guide rod with yoke
Operating pressure MPa	0.1 ... 1 MPa
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 ... 176 °F
Impact energy in end positions	0.295 ft-lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	93.296 lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	108.583 lbf
Moving mass with 0 mm stroke	4.319 oz
Additional mass factor per 10 mm of stroke	1.345 oz
Basic weight for 0 mm stroke	11.576 oz
Additional weight per 10 mm stroke	0.602 oz
Mounting type	with through hole with internal (female) thread with accessories Optional
Pneumatic connection	1/8 NPT
Material of flange screw	Steel
Material cover	Anodised wrought aluminium alloy
Material seals	NBR
Material of dynamic seals	TPE-U(PU)
Material end plate	Anodised wrought aluminium alloy
Material piston rod	High alloy steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy