


axial kit EAMM-A-L62-80G

Part number: 557989

★ Core product range

Suitable for electric drives.

FESTO



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	47 Nm
Product weight	1,620 g
Interface code, actuator	L62
Interface code, motor in	80G
Materials note	Conforms to RoHS