


Axial kit EAMM-A-A19-40A

Part number: 558894

FESTO

Suitable for cantilever axis EGSA.



Data sheet

Feature	Value
Size	19
Assembly position	Any
Max. speed	10,000 1/min
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Mass moment of inertia	1.06 kgmm ²
Transferable torque	2.3 Nm
Product weight	240 g
Materials note	Conforms to RoHS