


mini slide EGSL-BS-45-100-10P

Part number: 559335

FESTO



Data sheet

Feature	Value
Working stroke	100 mm
Size	45
Parallel running in the z-direction	0.04 mm
Parallelism	0.05 mm
Reversing backlash	≤ 50 μm
Spindle diameter	10 mm
Spindle pitch	10 mm/U
Assembly position	Any
Guide	Ball bearing cage guide
Design structure	Electric mini slide Guide With ball screw
Motor type	Stepper motor Servomotor
Spindle type	Ball screw
Position detection	For proximity sensor
Max. acceleration	25 m/s ²
Max. speed	1 m/s
Repetition accuracy	±0,015 mm
Duty cycle	100 %
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Sound pressure level	60 dB(A)
Protection class	IP40
Ambient temperature	0 ... 60 °C
Permanent feed force	100 N
Max. drive torque	0.51 Nm
Max. force F _y	631 N
Max. force F _z	631 N
Max. torque M _x	18.6 Nm
Max. torque M _y	16.3 Nm
Max. torque M _z	16.3 Nm
Max. radial force at drive shaft	120 N
Max. feed force F _x	150 N
No-load driving torque	0.08 Nm
Reference value for working load, horizontal	6 kg
Reference value for working load, vertical	6 kg
Mass moment of inertia J _L per kg of working load	0.0253 kgcm ²
Mass moment of inertia, J _O	0.0614 kgcm ²
Feed constant	10 mm/U
Maintenance interval	Life-time lubrication
Moving mass	670 g
Product weight	1,570 g
Mounting type	with internal (female) thread with centring sleeve with accessories

Feature	Value
Materials note	Conforms to RoHS
Material cover	Aluminium casting Painted
Material guide rail	Roller bearing steel
Material housing	Wrought Aluminium alloy Anodised
Material yoke plate	Wrought Aluminium alloy Anodised
Material spindle nut	Roller bearing steel
Material spindle	Roller bearing steel