

water separator MS6N-LWS


Part number: 564898

FESTO

Condensate drain through fully automatic condensate drain valve.



Exemplary representation



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	6
Series	MS
Assembly position	Vertical +/- 5°
Condensate drain	fully automatic
Design structure	Centrifugal separator
Max. condensate volume	38 ml
Bowl guard	integrated as metal shell
Degree of condensate separation	99 %
Operating pressure	0.8 ... 16 bar
Standard nominal flow rate	2,400 ... 3,800 l/min
Authorisation	c UL us - Recognized (OL)
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-:-:-] Compressed air in accordance with ISO8573-1:2010 [7:-:-] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Food-safe	See Supplementary material information
Medium temperature	-10 ... 60 °C
Protection class	IP65 to IEC 60529
Ambient temperature	-10 ... 60 °C
Mounting type	Line installation with accessories Optional
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	Aluminium die cast
Material bowl	Wrought Aluminium alloy
Material screen	PA