


# electrical connection box CAPC-F1-E-M12

Part number: 570042

FESTO



## Data sheet

Feature	Value
Dimensions W x L x H	50 mm x 148 mm x 28 mm
Fieldbus interface	2 x M12 socket, 5 pin
Operating voltage range DC	18 ... 30 V
Max. power supply	4 A
Nominal operating voltage DC	24 V
Authorisation	c UL us - Listed (OL)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Storage temperature	-20 ... 70 °C
PWIS conformity	VDMA24364-B2-L
Protection class	IP65 IP67
Ambient temperature	-5 ... 50 °C
Product weight	85 g
Cable length	20 m
Materials note	Conforms to RoHS
Material housing	PA