



# mini slide

## DGSL-4-20-EA

Part number: 570159

FESTO



## Data sheet

Feature	Value
Stroke	20 mm
Adjustable endposition range/front length	14.5 mm
Adjustable endposition range/rear length	3.5 mm
Piston diameter	6 mm
Operating mode of drive unit	Yoke
Cushioning	Short elastic cushioning rings/pads at both ends
Assembly position	Any
Guide	Ball bearing cage guide
Design structure	Yoke Piston Piston rod Slide
Position detection	For proximity sensor
Operating pressure MPa	0.25 ... 0.8 MPa
Operating pressure	2.5 ... 8 bar
Max. speed	0.5 m/s
Repetition accuracy	0,3 mm
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Impact energy in end positions	0.015 Nm
Cushioning length	0.9 mm
Max. force F <sub>y</sub>	368 N
Max. force F <sub>z</sub>	368 N
Max. torque M <sub>x</sub>	2 Nm
Max. torque M <sub>y</sub>	2 Nm
Max. torque M <sub>z</sub>	2 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	13 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	17 N
Moving mass	34 g
Product weight	95 g
alternative connections	See product drawing
Mounting type	with through hole
Pneumatic connection	M3
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	HNBR
Material housing	Wrought Aluminium alloy
Material piston rod	High alloy steel, non-corrosive